

F

E

D

C

B

A

F


E

D

C

B


A



PART NUMBER LEGEND

Ⓑ E66A06004M005

LENGTH
M005= 0.5 X LENGTH
M010= 1.0 X LENGTH
M100= 10.0 X LENGTH



Ⓑ

CABLE LENGTH TOLERANCES		
>.3M [1FT]:	+19mm-0 [+.75in-0]	
.3 - .9M [1 - 3FT]:	+44.5mm-0 [+1.75in-0]	
.9 - 1.8M [3 - 6FT]:	+55.6mm-0 [+2.19in-0]	
1.8 - 3.7M [6 - 12FT]:	+88.9mm-0 [+3.50in-0]	
3.7 - 7.3M [12 - 24FT]:	+165.1mm-0 [+6.50in-0]	
7.3-14.6M [24 - 48FT]:	+317.5mm-0 [+12.50in-0]	
14.6 - 30.5M [48-100FT]:	+622.3mm-0 [+24.50in-0]	
OVER 30M [100FT]	+2% OF FINISHED LENGTH	

NOTES:

1. MATERIALS: AS NOTED
2. FINISHES: AS NOTED
3. PACKAGING: PARTS ARE PLACED IN CLEAR POLY BAG WITH BAR-CODE LABEL ATTACHED
4. TIA/EIA RATING: CAT 5E
5. TEMPERATURE RATING: -20°C TO 75°C
6. JACKET RESISTANCE: WELD SLAG, SUN & OIL

Ⓑ

PART NO.	ENGINEERING NO.	FINISHED LENGTH
1201080687	E66A06004M005	0.5M [1'8"]
1201080557	E66A06004M010	1.0M [3'3"]
1201080561	E66A06004M100	10.0M [6'7"]

4	1	WRAP LABEL	VINYL	BLACK/YELLOW
3	2	BOOT (HOODED)	POLYOLEFIN	BLACK
2	2	RJ45 PLUG	PHOS BRNZ & PC	GOLD PLATE & CLEAR
1	1	CABLE, 24 AWG, 2 PAIR	TPE JACKET	TEAL
ITEM	QTY	COMPONENT	MATERIAL	FINISH

CORRECTED P/N LEGEND EC NO: IPG2019-0537 DRWN: RSTONE 6/4/19 CHKD: C CHRAST 2019/06/06 APPR: BWOODMAN2015/04/10		DESCRIPTION REV	QUALITY SYMBOLS	GENERAL TOLERANCES (UNLESS SPECIFIED)			DIMENSION STYLE INCH		SCALE ---	DESIGN UNITS INCH	THIRD ANGLE PROJECTION	
			▽=0 ▽C=0		mm	INCH	DRAWN BY DATE RSTONE 2015/04/06		TITLE MALE/MALE RJ45 CORDSET 2PR 10 BASE-T 24 AWG TEAL TPE CABLE			
				4 PLACES	±---	±---	CHECKED BY DATE B ARDEN 2015/04/08					
				3 PLACES	±---	±---	APPROVED BY DATE KJOZWIK 2015/04/10					
				2 PLACES	±---	±.01	MATERIAL NO. -		DOCUMENT NO. SD-120108-080		SHEET NO. 1 OF 1	
				1 PLACE	±---	±---						
				ANGULAR ±---°			SIZE B		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION			
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS												

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[1201080687](#)