

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1202530157](#)
Status: **Active**
Overview: [Contrinex Inductive and Photoelectric](#)
Description: Contrinex Inductive Sensor, M18 Housing, 0 - 20mm Operating Distance, Non-embeddable, Analog, 0 - 10V Output, 4-pin M12 Connector, 63.5mm Housing Length

Documents:
[Product Specification 1202530157-000 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Datasheet \(PDF\)](#)

General	
Product Family	Sensors
Series	120253
IP Rating	IP67
Overview	Contrinex Inductive and Photoelectric
Product Category	Inductive Sensors
Product Name	Contrinex
Type	Inductive
UPC	191130063277
Physical	
Connection	Connector (M12, 4-pin)
Length	63.5mm
Material - Housing	Chrome Plated Brass
Material - Sensing Face	PBTP
Mounting Style	Non-embeddable
Operating Distance	0 - 20mm
Output	0-10V
Sensor Housing Size	M18
Temperature Range - Operating	-25° to +70°C
Electrical	
Polarity	Analog
Material Info	
Engineering Number	DW-AS-519-M18-390
Reference - Drawing Numbers	
Product Specification	1202530157-000



Series image - Reference only

EU ELV Not Relevant	
EU RoHS Compliant with Exemption 6(c) REACH SVHC Not Reviewed Halogen-Free Status Not Reviewed For more information, please visit Contact US	China RoHS China ROHS 50 Image ELV Not Relevant RoHS Phthalates Not Contained

Search Parts in this Series
[120253](#) Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

120253-0157