

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1202530236

Status:

Active

Overview:

Contrinex Inductive and Photoelectric

Description:

Contrinex Inductive Sensor, M12 Housing, 4mm Operating Distance, Non-embeddable, PNP, NO, 4-pin M12 Connector, 60mm Housing Length



Documents:

Product Specification 1202530236-000 (PDF)

RoHS Certificate of Compliance (PDF)

Datasheet (PDF)

General

Product Family

Sensors

Series

120253

IP Rating

IP67

Overview

Contrinex Inductive and Photoelectric

Product Category

Inductive Sensors

Product Name

Contrinex

Type

Inductive

UPC

191130064069

Physical

Connection

Connector (M12, 4-pin)

Length

60mm

Material - Housing

Nickel Plated Brass

Material - Sensing Face

PBTP

Mounting Style

Non-embeddable

Operating Distance

4mm

Output

NO

Sensor Housing Size

M12

Temperature Range - Operating

-25° to +70°C

Electrical

Polarity

PNP

Switching Frequency

≤ 2000 Hz

Material Info

Engineering Number

DW-AS-613-M12

Reference - Drawing Numbers

Product Specification

1202530236-000

EU ELV

Not Relevant

EU RoHS

China RoHS

Compliant with Exemption 6(c)

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit

Contact US

China ROHS

50 Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

120253 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

120253-0236