

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1202530505](#)
Status: **Active**
Overview: [Contrinex Inductive and Photoelectric](#)
Description: Contrinex Inductive Sensor, M4 Housing, 1mm Operating Distance, Embeddable, PNP, NC, 2m 3-wire PUR Cable, 22mm Housing Length

Documents:
[Product Specification 1202530505-000 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Datasheet \(PDF\)](#)

General	
Product Family	Sensors
Series	120253
IP Rating	IP67
Overview	Contrinex Inductive and Photoelectric
Product Category	Inductive Sensors
Product Name	Contrinex
Type	Inductive
UPC	191130068708
Physical	
Connection	Cable (PUR 2m, 3-wire)
Length	22mm
Material - Housing	Stainless Steel
Material - Sensing Face	Polyester
Mounting Style	Embeddable
Operating Distance	1mm
Output	NC
Sensor Housing Size	M4
Temperature Range - Operating	-25° to +70°C
Electrical	
Polarity	PNP
Switching Frequency	≤ 3000 Hz
Material Info	
Engineering Number	DW-AD-624-M4
Reference - Drawing Numbers	
Product Specification	1202530505-000



EU ELV Not Relevant	
EU RoHS Compliant REACH SVHC Not Reviewed Halogen-Free Status Not Reviewed	China RoHS
China ROHS ELV RoHS Phthalates	Green Image Not Relevant Not Contained

Search Parts in this Series
[120253](#) Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

120253-0505