

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1202530666

Status:

Active

Overview:

Contrinex Inductive and Photoelectric

Description:

Contrinex Inductive Sensor, M30 Fully Stainless Steel, 40mm Operating Distance, Non-embeddable, NPN, NC, 2m 3-wire TPE Cable, 70.2mm Housing Length



Series image - Reference only

Documents:

Product Specification 1202530666-000 (PDF)

RoHS Certificate of Compliance (PDF)

Datasheet (PDF)

General	
Product Family	Sensors
Series	120253
IP Rating	IP68, IP69K
Overview	Contrinex Inductive and Photoelectric
Product Category	Inductive Sensors
Product Name	Contrinex
Type	Inductive
UPC	191130065967
Physical	
Connection	Cable (TPE-S 2m, 3-wire)
Length	70.2mm
Material - Housing	Stainless Steel
Material - Sensing Face	Stainless Steel
Mounting Style	Non-embeddable
Operating Distance	40mm
Output	NC
Sensor Housing Size	M30
Temperature Range - Operating	-25° to +85°C
Electrical	
Polarity	NPN
Switching Frequency	≤ 90 Hz
Material Info	
Engineering Number	DW-LD-712-M30
Reference - Drawing Numbers	
Product Specification	1202530666-000

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Reviewed	
Halogen-Free	
Status	
Not Reviewed	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

120253 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[120253-0666](#)