

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1202540063

Status:

Active

Overview:

Contrinex Inductive and Photoelectric

Description:

Contrinex Photoelectric Sensor, 4mm Diameter Smooth Housing, Through-Beam (Receiver), 250mm Operating Distance, PNP, Dark-ON, 2m 3-wire PVC Cable, 35mm Housing Length



Documents:

Product Specification 1202540063-000 (PDF)

RoHS Certificate of Compliance (PDF)

Datasheet (PDF)

|                               |                                       |
|-------------------------------|---------------------------------------|
| General                       |                                       |
| Product Family                | Sensors                               |
| Series                        | 120254                                |
| IP Rating                     | IP67                                  |
| Operating Principle           | Through-Beam (Receiver)               |
| Overview                      | Contrinex Inductive and Photoelectric |
| Product Category              | Photoelectric Sensors                 |
| Product Name                  | Contrinex                             |
| Type                          | Photoelectric                         |
| UPC                           | 191130067398                          |
| Physical                      |                                       |
| Connection                    | Cable (PVC 2m, 3-wire)                |
| Length                        | 35mm                                  |
| Material - Housing            | Stainless Steel                       |
| Material - Window             | Glass                                 |
| Operating Distance            | 250mm                                 |
| Output                        | Dark-ON                               |
| Sensor Housing Size           | 4mm dia. (smooth)                     |
| Temperature Range - Operating | 0° to +55°C                           |
| Electrical                    |                                       |
| Polarity                      | PNP                                   |
| Switching Frequency           | ≤ 250 Hz                              |
| Material Info                 |                                       |
| Engineering Number            | LLR-D04MA-NMK-404                     |
| Reference - Drawing Numbers   |                                       |
| Product Specification         | 1202540063-000                        |

|                                                               |               |
|---------------------------------------------------------------|---------------|
| EU ELV                                                        |               |
| Not Relevant                                                  |               |
| EU RoHS                                                       | China RoHS    |
| Compliant                                                     |               |
| REACH SVHC                                                    |               |
| Not Reviewed                                                  |               |
| Halogen-Free                                                  |               |
| Status                                                        |               |
| Not Reviewed                                                  |               |
| For more information, please visit <a href="#">Contact US</a> |               |
| China ROHS                                                    | Green Image   |
| ELV                                                           | Not Relevant  |
| RoHS Phthalates                                               | Not Contained |

Search Parts in this Series

120254 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

120254-0063