

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1202540117](#)
Status: **Active**
Overview: Contrinex Inductive and Photoelectric
Description: Contrinex Photoelectric Sensor, M18 Plastic Housing, Diffuse, 3 - 1200mm Operating Distance, NPN, Changeover, Potentiometer Sensitivity Adjustment, 4-pin M12 Connector, 37mm Housing Length

Documents:
[Product Specification 1202540117-000 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Datasheet \(PDF\)](#)

General	
Product Family	Sensors
Series	120254
IP Rating	IP67
Operating Principle	Diffuse
Overview	<u>Contrinex Inductive and Photoelectric</u>
Product Category	Photoelectric Sensors
Product Name	Contrinex
Type	Photoelectric
UPC	191130068531
Physical	
Connection	Connector (M12, 4-pin)
Length	37mm
Material - Housing	ABS
Material - Window	PMMA
Operating Distance	3 - 1200mm
Output	Changeover
Sensor Housing Size	M18
Temperature Range - Operating	-25° to +55°C
Electrical	
Polarity	NPN
Switching Frequency	≤ 1500 Hz
Material Info	
Engineering Number	LTR-M18PA-PMS-101
Reference - Drawing Numbers	
Product Specification	1202540117-000



Series image - Reference only

EU ELV Not Relevant	
EU RoHS Compliant REACH SVHC Not Reviewed Halogen-Free Status Not Reviewed	China RoHS
For more information, please visit Contact US	
China ROHS ELV RoHS Phthalates	Green Image Not Relevant Not Contained

Search Parts in this Series
[120254](#) Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

[120254-0117](#)