

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1203410753](#)
Status: **Active**
Overview:
Description: Micro-Change M12 to Standard RJ-45 CAT6A Double-Ended Cordset, 8 Poles, Female (Straight) to Male RJ-45 (Straight), 26 AWG, Shielded PUR Cable, 3.0m (9.84') Length

Agency Certification	
UL	E200650
General	
Product Family	Industrial Cordsets
Series	120341
Connector End A	Micro-Change (M12)
Connector End B	RJ-45 (standard)
IP Rating	IP20, IP67
Material - Contact	Brass
Overview	brad_industrial_ethernet_solutions
Performance Category	6A
Product Name	Micro-Change (M12) Cat6A, RJ45
Region	America, Asia, Europe
Type	Double Ended
UPC	887191906645
Physical	
Cable Diameter	6.40mm (.252")
Cable Length	3.0m (9.84')
Color - Cable Jacket	Blue
Coupling Style	Threaded
Gender	Female-Male
Keyway	X-coded
LED Indicator	No
Material - Cable Jacket	PUR
Material - Connector Body	PUR
Material - Coupling Nut	Nickel-plated Brass
Material - O-Ring	Fluoro-elastomer
Material - Plating Mating	Gold
Net Weight	190.509/g
Orientation	Straight to Straight
Poles	8
Temperature Range - Operating	-40°C to +70°C
Wire Size AWG	26
Wire/Cable Type	Shielded PUR
Electrical	
Current - Maximum per Contact	0.5A
Voltage - Maximum	48V
Material Info	
Engineering Number	ERWPEU7020M030
Reference - Drawing Numbers	
Packaging Specification	PK-120341-170-001
Sales Drawing	1203410750-000

EU ELV

Not Reviewed

EU RoHS

Compliant with Exemption 6(c)

REACH SVHC

Contained Per -
D(2020)9139-DC (19
Jan 2021)
Lead

Halogen-Free

Status

Not Relevant

For more information, please visit [Contact US](#)

China RoHS

China ROHS	Not Relevant
ELV	Not Reviewed
RoHS Phthalates	Not Contained

Search Parts in this Series

[120341](#) Series

Mates With

[120341](#) Micro-Change CAT6A Plugs

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

1203410753