

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1210350156](#)
Status: **Active**
Overview: [mPm DIN Valve Connectors](#)
Description: Micro-Change (M12) to Brad mPm DIN Form A - 18mm Cordset, 5 Poles, Male (Straight) to Male (90°), 1.0m (3.28') Length

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Industrial Cordsets
Series	121035
Connector End A	Brad mPm DIN A - 18mm
Connector End B	Micro-Change (M12)
IP Rating	IP65
Material - Contact	Copper Alloy
Overview	mPm DIN Valve Connectors
Product Name	Micro-Change (M12), mPm
Protocol	N/A
Region	America, Europe
Type	Double Ended
UPC	883906501518

Physical

Cable Diameter	5.72mm (.225")
Cable Length	1.0m (3.28')
Color - Cable Jacket	Black
Coupling Style	Threaded
Gender	Male-Male
Keyway	Single
LED Indicator	No
Material - Cable Jacket	PUR
Material - Connector Body	Polypropylene
Material - Coupling Nut	Nickel-plated Brass
Material - Plating Mating	Gold
Orientation	90° to Straight
Poles	5
Temperature Range - Operating	-25° to +75°C
Wire Size AWG	22
Wire/Cable Type	Shielded PUR

Electrical

Current - Maximum per Contact	1.5A
Voltage - Maximum	N/A

Material Info

Engineering Number	E85000P12M010
--------------------	---------------

Reference - Drawing Numbers

Sales Drawing	SD-121036-001-001
---------------	-------------------

Image coming soon

Series image - Reference only

EU ELV

Not Relevant

EU RoHS

**Compliant with
Exemption 6(c)**

REACH SVHC

Contained Per -
D(2020)9139-DC (19
Jan 2021)
Lead

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS	50 Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

[121035](#) Series

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

[1210350156](#)