

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1212050003](#)
Status: **Active**
Overview: mPm DIN Valve Connectors
Description: mPm DIN Valve Connector, Form C-Micro 9.4mm, External Thread, 2 Pole Plus Ground Terminal, 250V AC/DC, Black, Profiled NBR Gasket, UL94-V0, Single Bag, Unmounted

Documents:

[Drawing \(PDF\)](#) [Packaging Specification PK-121205-C29-001 \(PDF\)](#)
[Product Specification PS-121201-001-001 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Product Specification STR-1299-001 \(PDF\)](#)

General

Product Family Field Attachable / Accessories
Series [121205](#)
Form C - Micro 9.4mm
IP Rating IP67
Material - Contact Brass
Overview [mPm DIN Valve Connectors](#)
Product Name mPm
Type Field Attachable Connector
UPC 884982367739

Physical

Cable Diameter 3.00-5.50mm
Coupling Type External Thread
Diagnostics / LEDs No
Diagnostics Port No
Gender N/A
Keyway None
Material - Connector Body Polyamide
Material - Coupling Nut N/A
Material - Plating Mating Silver
Net Weight 856.000/g
Orientation 90° Angle
Pitch - Mating Interface 9.40mm
Poles 2
Temperature Range - Operating -40°C to +90°C
Wire Size AWG 18

Electrical

Current - Maximum per Contact 16.0A
Voltage - Maximum 250V AC/DC

Material Info

Engineering Number C29200W0TSA

Reference - Drawing Numbers

Packaging Specification PK-121205-C29-001
Product Specification PS-121201-001-001, STR-1299-001
Sales Drawing SD-121205-001-001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant with Exemption 6(c)

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China RoHS

China ROHS	50 Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

[121205 Series](#)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

1212050003