

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1212110032](#)
Status: **Active**
Overview: mPm DIN Valve Connectors
Description: mPm DIN Valve Connector, Form C - Micro 9.4mm, External Threads, 2 Pole Plus Ground with C4 Circuit, 24V, Yellow LED + VDR, Transparent, Profiled NBR Gasket, Single Bag, Unmounted



Documents:
[Drawing \(PDF\)](#)
[Product Specification PS-121201-001-001 \(PDF\)](#)
[Product Specification STR-1251-001 \(PDF\)](#)
[Product Specification STR-1299-001 \(PDF\)](#)
[Packaging Specification PK-121211-S29-001 \(PDF\)](#)
[RoHS Certificate of Compliance \(PDF\)](#)

General
Product Family Field Attachable / Accessories
Series [121211](#)
Form C - Micro 9.4mm
IP Rating IP67
Material - Contact Brass
Overview [mPm DIN Valve Connectors](#)
Product Name mPm
Type Field Attachable Connector
UPC 884982530843

Physical
Cable Diameter 3.00-5.50mm
Coupling Type External Thread
Diagnostics / LEDs Yes
Diagnostics Port No
Gender N/A
Keyway None
Material - Connector Body Polyamide
Material - Coupling Nut N/A
Material - Plating Mating Silver
Net Weight 15.103/g
Orientation 90° Angle
Pitch - Mating Interface 9.40mm
Poles 2
Temperature Range - Operating -40°C to +90°C
Wire Size AWG 18

Electrical
Current - Maximum per Contact 16.0A
Voltage - Maximum 24V

Material Info
Engineering Number S29200TC420T

Reference - Drawing Numbers
Packaging Specification PK-121211-S29-001
Product Specification PS-121201-001-001, STR-1251-001, STR-1299-001
Sales Drawing SD-121211-001-001

EU ELV
Not Compliant

EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - D(2021)4569-DC (8 July 2021)	
Halogen-Free	
Status	
Not Relevant	
For more information, please visit Contact US	
China ROHS	Not Relevant
ELV	Not Compliant
RoHS Phthalates	Not Contained

Search Parts in this Series
[121211](#) Series

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

[1212110032](#)