

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1300150109

Status:

Active

Overview:

Brad Mini-Change Connectors

Description:

Mini-Change C-Size Receptacle, 19 Poles, 1/2" - 14 NPT Threads, Male (Straight) to Leads, 0.30m (11.81") Length

Documents:

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

General

Product Family

Industrial Receptacles

Series

130015

Comments

C-Size (1-1/8" - 16 UN-2A)

IP Rating

IP67

Overview

Brad Mini-Change Connectors

Product Name

Mini-Change

Type

Single Ended (pigtail)

UPC

78678841464

Physical

Coupling Type

External Thread

Gender

Male

Keyway

Single

Length

0.30m

Material - Component

Gray Anodized Aluminum

Mounting Thread Size

PG16

Net Weight

90.718/g

Orientation

Straight

Panel Mount

Front

Poles

19

Temperature Range - Operating

-20° to +80°C

Wire Size AWG

18, 22

Wire/Cable Type

UL 1569

Electrical

Current - Maximum per Contact

2.0A

Voltage - Maximum

300V AC/DC

Material Info

Engineering Number

3R3N36E80C300

Reference - Drawing Numbers

Sales Drawing

SD-130015-009-001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant with Exemption 6(c)

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Relevant

For more information, please visit [Contact US](#)

China ROHS

Not Relevant

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

130015 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

[1300150109](#) [3R3N36E80C300](#)