

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1300580025

Status:

Active

Overview:

Brad Industrial Ethernet Solutions

Description:

Ultra-Lock (M12) D-Coded to RJ-45 Adapter, Straight to Straight, 4-Pole Female to RJ45 Male, Unshielded PVC, 1.0m (3.28') Length

Documents:	
Drawing (PDF)	RoHS Certificate of Compliance (PDF)

Agency Certification	
UL	E200650
General	
Product Family	Industrial Receptacles
Series	130058
IP Rating	IP67
Overview	Brad Industrial Ethernet Solutions
Product Name	RJ45, Ultra-Lock (M12)
Type	Double Ended
UPC	78678802441
Physical	
Coupling Type	Push to Lock
Gender	Female-Male
Keyway	D-coded
Length	1.0m
Material - Component	Nickel-plated Brass
Mounting Thread Size	PG9
Net Weight	150.000/g
Orientation	Straight
Panel Mount	Back
Poles	4
Temperature Range - Operating	-25° to +80°C
Wire Size AWG	24
Wire/Cable Type	Unshielded PVC
Electrical	
Current - Maximum per Contact	0.5A
Voltage - Maximum	250V AC/DC
Material Info	
Engineering Number	ERWPAB3002M010
Reference - Drawing Numbers	
Sales Drawing	SD-130054-002-001



EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant with Exemption 6(c)	
REACH SVHC	
Contained Per - D(2020)4578-DC (25 June 2020)	
Lead	
Halogen-Free	
Status	
Not Low-Halogen	
For more information, please visit Contact US	
China ROHS	50 Image
ELV	Not Relevant
RoHS Phthalates	Not Contained
ZZCERT_CE - Declaration of Conformity	CER_4000380967_00_000.pdf

Search Parts in this Series
130058 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

1300580025 ERWPAB3002M010