

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1301430193

Status:

Active

Overview:

Watertite Extreme Wet-Location Wiring Solutions

Description:

Watertite Extreme Cordset 16 Gauge SOOW, 2 Pole/3 Wire, Cordset Length 15.24m (50.0'), NEMA L5-15, 125V

Documents:

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

Brochure (PDF)

|                               |                                                 |
|-------------------------------|-------------------------------------------------|
| Agency Certification          |                                                 |
| CSA                           | LR6837                                          |
| UL                            | E38085                                          |
| General                       |                                                 |
| Product Family                | Wiring Devices                                  |
| Series                        | 130143                                          |
| IP Rating                     | IP67                                            |
| NEMA Configuration            | NEMA L5-15                                      |
| Overview                      | Watertite Extreme Wet-Location Wiring Solutions |
| Product Name                  | Watertite Extreme                               |
| Receptacle Type               | Single                                          |
| Specialty                     | N/A                                             |
| Type                          | Cordset                                         |
| UPC                           | 78678879690                                     |
| Physical                      |                                                 |
| Cord Grip Body Size           | F2 1/2"                                         |
| Flange                        | No                                              |
| Flip Lid                      | No                                              |
| Gender                        | Male-Female                                     |
| Length                        | 15.24m (50.0')                                  |
| Locking Blade                 | Yes                                             |
| Net Weight                    | 265.000/kg                                      |
| Poles                         | 2-pole/3-wire                                   |
| Electrical                    |                                                 |
| Cord Type                     | 12/3 SOOW                                       |
| Current - Maximum per Contact | 15.0A                                           |
| GFCI                          | No                                              |
| Lighted Connector             | No                                              |
| Voltage - Maximum             | 125V                                            |
| Material Info                 |                                                 |
| Engineering Number            | 24W47B163                                       |
| Reference - Drawing Numbers   |                                                 |
| Sales Drawing                 | 1301430187-000                                  |



Series image - Reference only

|                                                               |              |
|---------------------------------------------------------------|--------------|
| EU ELV                                                        |              |
| Not Relevant                                                  |              |
| EU RoHS                                                       | China RoHS   |
| Not Relevant                                                  |              |
| REACH SVHC                                                    |              |
| Not Relevant                                                  |              |
| Halogen-Free                                                  |              |
| Status                                                        |              |
| Not Relevant                                                  |              |
| For more information, please visit <a href="#">Contact US</a> |              |
| China ROHS                                                    | Not Relevant |
| ELV                                                           | Not Relevant |
| RoHS Phthalates                                               | Not Relevant |

Search Parts in this Series

130143 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

[1301430193](#) [24W47B163](#)