

PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION

**Part Number:** [1301470079](#)  
**Status:** **Active**  
**Overview:** [Watertite Extreme Wet-Location Wiring Solutions](#)  
**Description:** Watertite Extreme Plug with Locking Blade, 3 Pole/4 Wire, NEMA L15-30, 3ø 250V, Cord Grip Body Size F4

**Documents:**

[Brochure \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

**Agency Certification**

CSA LR6837  
UL E10176

**General**

Product Family Wiring Devices  
Series [130147](#)  
IP Rating IP67  
NEMA Configuration NEMA L15-30  
Overview [Watertite Extreme Wet-Location Wiring Solutions](#)  
Product Name Watertite Extreme  
Receptacle Type N/A  
Specialty N/A  
Type Plug  
UPC 78678871233

**Physical**

Cord Grip Body Size F4 1"  
Flange No  
Flip Lid No  
Gender Male  
Length N/A  
Locking Blade Yes  
Net Weight 295.741/g  
Poles 3-pole/4-wire

**Electrical**

Cord Type N/A  
Current - Maximum per Contact 30.0A  
GFCI No  
Lighted Connector No  
Voltage - Maximum 3Ø 250V

**Material Info**

Engineering Number 28W75



Series image - Reference only

**EU ELV**

**Not Relevant**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

For more information, please visit [Contact US](#)

|                 |              |
|-----------------|--------------|
| China ROHS      | Not Reviewed |
| ELV             | Not Relevant |
| RoHS Phthalates | Not Reviewed |

**Search Parts in this Series**

[130147](#) Series

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

[1301470079](#) [28W75](#)