

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0150180358

Status:

Active

Overview:

Description:

0.50mm Pitch Premo-Flex FFC Jumper with Ears, Opposite Side Contacts (Type D), 305.00mm Cable Length, Gold (Au) Plating, 32 Circuits

General	
Product Family	Cable
Series	15018
Comments	Opposite Side Contacts, Type D
Crimp Quality Equipment	Yes
Overview	premo flex
Product Name	Premo-Flex FFC Jumper
UPC	193264331826
Physical	
Cable Length	305.00mm
Circuits (Loaded)	32
Contact Layout Type	D (opposite side)
Material - Plating Mating	Gold
Packaging Type	Bag
Pitch - Mating Interface	0.50mm
Temperature Range - Operating	-40° to +105°C
Wire Size AWG	N/A
Wire/Cable Type	Flat Flex Cable
Electrical	
Current - Maximum per Contact	0.5A
Voltage - Maximum	60V AC
Material Info	
Reference - Drawing Numbers	
Product Specification	150180001-000
Sales Drawing	SD-15018-001-001

EU ELV

Not Relevant

EU RoHS

China RoHS

Compliant

REACH SVHC

Not Contained Per - D(2021)4569-DC (8 July 2021)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

15018 Series

Mates With

Easy-On FFC/FPC Connector [5051103291](#)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

15018-0358