

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0700581096

Status:


Active

Overview:

SL Modular Connectors

Description:

SL Crimp Terminal, Female, 24-30 AWG, with Tin (Sn) Plated Contact, Bag



Documents:

Drawing (PDF)

Product Specification PS-70058-001 (PDF)

Product Specification PS-70058-001 (PDF)

Product Specification PS-70400-001 (PDF)

RoHS Certificate of Compliance (PDF)

General	
Product Family	Crimp Terminals
Series	70058
Application	Signal
Crimp Quality Equipment	Yes
Overview	SL Modular Connectors
Packaging Alternative	700581069 (Reel)
Product Name	CyClone, SL
UPC	191128284349
Physical	
Gender	Female
Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.075/g
Packaging Type	Bag
Plating min - Mating	3.810µm
Plating min - Termination	3.810µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.52mm max.
Wire Size AWG	24, 26, 28, 30
Wire Size mm²	N/A

Material Info

Reference - Drawing Numbers	
Product Specification	PS-70058-001, PS-70400-001
Sales Drawing	700580000-SD-000

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per -
D(2021)4569-DC (8
July 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

70058 Series

Use With

SL Crimp Housing [70066](#) , [70450](#)

CyClone Connector [73099](#)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[70058-1096](#)