

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: 0936012926

Status: Active

Overview: GWconnect® Heavy Duty Connectors (HDC)

Description: GWconnect STD-HV - Standard-High Voltage, Single Lever Surface Mount Housing, Bottom Entry M32 Gable Gland, Die-cast Aluminum, with 1 Lever, with Cover, with Gasket, Size 16B «77x27», High Construction, Grey

Documents:
RoHS Certificate of Compliance (PDF)

Agency Certification	
CSA	256883
UL	E249674
General	
Product Family	Industrial Connectors / Enclosures
Series	93601
Component Size	16B «77X27»
Component Type	Single Lever SMT Housing
IP Rating	IP66, IP69
Overview	GWconnect® Heavy Duty Connectors (HDC)
Product Category	Heavy Duty Connectors
Product Name	GWconnect
Standard	ANSI/UL 50, ANSI/UL 50 E, CSA C22.2 No.94-1-2, EN 61984
Type	STD-HV
UPC	887191858654
Physical	
Cover Coating	Polyester Powder
Cover Color	Grey RAL 7037
Entry Location	Bottom
Housing Coating	Polyester Powder
Housing Color	Grey RAL 7037
Lock to Mating Part	Yes
Material - Cover	Die-cast Aluminum
Material - Gasket	NBR
Material - Housing	Die-cast Aluminum
Material - Lever	Galvanized Steel
Mounting Style	Surface Mount
Number of Levers	1
Packaging Type	Bag
Thread Size	M32
Thread Type	(M) Metric
Electrical	
Voltage - Maximum	830V
Material Info	
Engineering Number	7816.7083.2



Series image - Reference only

EU ELV
Not Reviewed

EU RoHS **China RoHS**
Not Reviewed

REACH SVHC
Not Reviewed

Halogen-Free
Status
Not Reviewed

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series
93601 Series

Use With
Size 16B «77x27» , S-EHV Inserts with Screw Terminals and S-HSB Inserts

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

93601-2926