

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: 0936013355

Status: Active

Overview: GWconnect® Heavy Duty Connectors (HDC)

Description: GWconnect HE - Harsh Environment, Double Lever Surface Mount Housing, Die-cast Aluminum, with 4 Pegs, Side Entry, with Gasket, Size 24B «104x27», Pg21 Thread, High Construction, Black



Documents:
RoHS Certificate of Compliance (PDF)

Agency Certification	
CSA	256883
UL	E249674
General	
Product Family	Industrial Connectors / Enclosures
Series	93601
Component Size	24B «104X27»
Component Type	Double Lever SMT Housing
IP Rating	IP66, IP69
Overview	GWconnect® Heavy Duty Connectors (HDC)
Product Category	Heavy Duty Connectors
Product Name	GWconnect
Standard	ANSI/UL 50, ANSI/UL 50 E, CSA C22.2 No.94-1-2, EN 61984
Type	HE
UPC	887191885964
Physical	
Housing Coating	Polyester Powder
Housing Color	Black RAL 9005
Lock to Mating Part	Yes
Material - Gasket	NBR
Material - Housing	Die-cast Aluminum
Material - Peg	Stainless Steel
Mounting Style	Surface Mount
Number of Pegs	4
Packaging Type	Bag
Thread Size	Pg21
Thread Type	(Pg)
Electrical	
Voltage - Maximum	500V
Material Info	
Engineering Number	7824.5151.1

EU ELV
Not Reviewed

EU RoHS **China RoHS**
Not Reviewed

REACH SVHC
Not Reviewed

Halogen-Free
Status
Not Reviewed

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series
93601 Series

Use With
Size 24B «104x27» S-D, S-DD, S-E, S-EE, S-EP, S-ES, S-HSB, S-ESHV, S-K, S-M, and S-EHV Inserts with Crimp Contacts

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[93601-3355](#)