

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: 0936014650
Status: Active
Overview: GWconnect® Heavy Duty Connectors (HDC)
Description: Gwconnect STD - Standard S-CX/3A Shielded 50 Ohm Coaxial Connector with Housing, 1 Lever , Female, 1-Pole, Size 3A «21x21», Black

Documents:
RoHS Certificate of Compliance (PDF)

General	
Product Family	Industrial Connectors / Enclosures
Series	93601
Comments	Contact to be ordered Separately.
Component Size	3A «21x21»
Component Type	Coaxial Connector
IP Rating	IP66, IP67
Insert Series	S-CX
Overview	GWconnect® Heavy Duty Connectors (HDC)
Product Category	Heavy Duty Connectors
Product Name	GWconnect®
Standard	CSA C22.2 NO. 182.3, EN 60664-1, EN 61984, UL 1977
Type	STD
UPC	887191840246
Physical	
Durability (mating cycles max)	500
Flammability	UL 94V-0
Gender	Female
Housing Coating	Epoxy-Polyester Powder
Housing Color	Black RAL 9005
Lock to Mating Part	Yes
Material - Housing	Die-cast Aluminum
Material - Insert	Polycarbonate
Material - Lever	Stainless Steel
Material - Shield/Shell	Zinc Alloy-Nickel Plated
Packaging Type	Bag
Polarized to Mating Part	Yes
Poles	1
Temperature Range - Operating	-40°C to +85°C
Wire Size AWG	26-12
Wire Size mm²	0.14-4.00
Electrical	
Current - Maximum per Contact	10.0A
Voltage	EN 61984: 50V 0.8kV 3
Material Info	
Engineering Number	7903.4512.0



Series image - Reference only

EU ELV Not Reviewed	
EU RoHS Not Reviewed	China RoHS
REACH SVHC Not Reviewed	
Halogen-Free Status	
Not Reviewed	
Need more information on product environmental compliance?	
Email productcompliance@molex.com Please visit the Contact Us section for any non-product compliance questions.	
China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series
93601 Series

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

93601-4650