

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0936014828](#)
Status: **Active**
Overview: [GWconnect Heavy Duty Connectors \(HDC\)](#)
Description: GWconnect STD - Standard Socket Coupler Assembly, Size 3A «21x21», 8p/8C + 2pC-to-8p/8C + 2pC Pin-to-Pin Wiring, 2 Die-cast Aluminum Bulkhead Housings, with Gasket, 2 Metal Levers, Grey

Documents:
[RoHS Certificate of Compliance \(PDF\)](#)

General	
Product Family	Industrial Connectors / Enclosures
Series	93601
Adapter Color	Grey White RAL 9002
Comments	PCB assembled
Component Size	3A «21x21»
Component Type	Coupler
IP Rating	IP66, IP67
Overview	GWconnect Heavy Duty Connectors (HDC)
Product Category	Modular Plugs / Jacks
Product Name	GWconnect
Type	RJ45 CAT5
UPC	887191852812
Physical	
Flammability	UL 94V-0
Housing Coating	Polyester Powder
Housing Color	Grey RAL 7037
Lock to Mating Part	Yes
Material - Adapter	Polyamide
Material - Gasket	NBR
Material - Housing	Die-cast Aluminum
Material - Lever	Stainless Steel
Material - Plating	Gold
Mounting Style	Panel
Number of Levers	2
Packaging Type	Bag
Polarized to Mating Part	Yes
Poles	8p/8C + 2pC
Temperature Range - Operating	-40° to +120°C
Material Info	
Engineering Number	7982.3414.0



Series image - Reference only

EU ELV Not Reviewed	
EU RoHS Not Reviewed	China RoHS
REACH SVHC Not Reviewed	
Halogen-Free Status Not Reviewed	
For more information, please visit Contact US	
China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series
[93601](#) Series

Mates With
Patch Cords

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[93601-4828](#)