

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0936060012](#)
Status: **Active**
Overview: [GWconnect Heavy Duty Connectors \(HDC\)](#)
Description: [GWconnect Data Interface, with 1- 25 Pole D-Sub Gender Changer Connector](#)

Documents:
[RoHS Certificate of Compliance \(PDF\)](#)

General	
Product Family	Industrial Connectors / Enclosures
Series	93606
Component Size	32A «66x40»
Component Type	D-sub Interface
Overview	GWconnect Heavy Duty Connectors (HDC)
Product Category	Heavy Duty Connectors
Product Name	GWconnect
UPC	887191822105
Physical	
Lock to Mating Part	Yes
Net Weight	36.000/g
Packaging Type	Bag
Poles	25
Temperature Range - Operating	-25° to +125°C
Electrical	
Current - Maximum per Contact	3.0A
Voltage - Maximum	125V AC / 150V DC
Material Info	
Engineering Number	2000.3021.0

EU ELV Not Reviewed	
EU RoHS Not Reviewed REACH SVHC Not Reviewed Halogen-Free Status Not Reviewed	China RoHS
For more information, please visit Contact US	
China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

- Search Parts in this Series**
[93606](#) Series
- Mates With**
Data Interface D-Sub Cable Assemblies.
- Use With**
Size 32A «66x40» Bulkhead Housings.

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[93606-0012](#)