

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1068151818](#)
Status: **Active**
Overview: Polymicro Capillary Tubing
Description: Polymicro Flexible Fused Silica Capillary Tubing, Inner Diameter 300µm, Outer Diameter 665µm, TSP300665

Documents:

[Datasheet \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family Capillary Tubing
Series [106815](#)
Application Industrial, Medical, Research, Scientific, and other
Application Notes and Articles www.molex.com/polymicro/literature.html
Capillary Configurator www.molex.com/polymicro/capillaryconfigurator.html
Capillary Series TSP
Catalog www.molex.com/polymicro/catalog.html
Overview Polymicro Capillary Tubing
Polymicro Yes
Product Name Thick Wall
Type Capillary Tubing
UPC 883906649449

Physical

Coating Thickness per Side 24µm nominal
Cutting Style Laser Cut, Precision Cleave, Saw Cut, Standard Cleave
Internal Diameter 300µm
Internal Diameter Tolerance ± 6µm
Material - Coating Standard Polyimide
Material - Tubing Synthetic Fused Silica
Net Weight 0.581/g
Outer Diameter 665µm
Outer Diameter Tolerance ± 15µm
Packaging Type Spool
Proof Tested @ Minimum 100kpsi 100% for Strength
Temperature Range - Operating -65° to +350°C
Tubing Length 10.0m minimum

Material Info

Engineering Number 2001818



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2021)4569-DC (8
July 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China RoHS

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

[106815](#) Series

Use With

www.molex.com/polymicro/capillarytubingaccessories

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

106815-1818