

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1120365102

Status:

Active

Overview:

Industrial Remote Access

Description:

Secured Industrial Router, 4G EU Interface, 4 Port Switch, IP20

Documents:

RoHS Certificate of Compliance (PDF)

Product Literature (PDF)

General	
Product Family	Servers and Routers
Series	112036
Approvals	CE certified, UL certified
Digital Interface	2
Exclude SD Check	Yes
IP Rating	IP20
Interface	4G
Overview	Industrial Remote Access
Product Category	Router
Product Literature Order No	987651-6672
Product Name	Industrial Secured Router
Software Downloads	DRL-ISR-10x
Switch - Number of Ports	4
UPC	191128243810
USB Interface	1
Physical	
Connectivity	RJ45
Dimensions	69.00 x 38.50 x 92.50mm
Humidity - Operating	0 to 95%
Mounting Style	DIN Rail
Temperature Range - Operating	-40° to +70°C
Material Info	
Engineering Number	DRL-ISR-102



Series image - Reference only

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Not Reviewed	
REACH SVHC	
Not Reviewed	
Halogen-Free	
Status	
Not Reviewed	
For more information, please visit Contact US	
China ROHS	Not Reviewed
ELV	Not Relevant
RoHS Phthalates	Not Reviewed

Search Parts in this Series

112036 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[112036-5102](#)