

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1122190006

Status:

Active

Overview:

Woodhead ArcArrest Connector System

Description:

Woodhead ArcArrest Receptacle, Switch-Rated, 30.0A, 208V AC, 3-Pole+Ground, Insulator Keying Position 16



Documents:

[Drawing \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)

[Brochure \(PDF\)](#)

Agency Certification	
UL	E145923
General	
Product Family	Wiring Devices
Series	112219
IP Rating	IP69K
NEMA Configuration	N/A
Overview	Woodhead ArcArrest Connector System
Product Name	ArcArrest
Receptacle Type	Single
Specialty	Switch-Rated
Type	Receptacle
UPC	78172552823
Wire Size AWG	8 to 12
Physical	
Flange	Yes
Flip Lid	Yes
Gender	Female
Length	87.16mm (3.431")
Locking Blade	N/A
Net Weight	98.540/g
Poles	3
Electrical	
Cord Type	N/A
Current - Maximum per Contact	30.0A
GFCI	No
Lighted Connector	No
Voltage - Maximum	208V AC
Material Info	
Engineering Number	ARC30FC03
Reference - Drawing Numbers	
Sales Drawing	1122190010-000

EU ELV

Not Relevant

EU RoHS

Not Reviewed

China RoHS

Not Reviewed

REACH SVHC

Contained Per - ED/01/2018 (15 January 2018) 2,4-Di-tert-butyl-6-(5-chlorobenzotriazol-2-yl)p

Halogen-Free

Status

For more information, please visit

Contact US

China ROHS

50 Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

112219 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[1122190006](#)