

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1122190053

Status:

Active

Overview:

Woodhead ArcArrest Connector System

Description:

Woodhead ArcArrest 70° Angle Receptacle, Switch-Rated, 30.0A, 277/480V AC, 3-Pole+Neutral+Ground, Insulator Keying Position 4



Series image - Reference only

Documents:

[Drawing \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)

[Brochure \(PDF\)](#)

Agency Certification	
UL	E145923
General	
Product Family	Wiring Devices
Series	112219
IP Rating	IP69K
NEMA Configuration	N/A
Overview	Woodhead ArcArrest Connector System
Product Name	ArcArrest
Receptacle Type	Single
Specialty	Switch-Rated
Type	Receptacle
UPC	78172559230
Wire Size AWG	8 to 12
Physical	
Flange	Yes
Flip Lid	Yes
Gender	Female
Length	110.30mm (4.340")
Locking Blade	N/A
Net Weight	98.540/g
Poles	3
Electrical	
Cord Type	N/A
Current - Maximum per Contact	30.0A
GFCI	No
Lighted Connector	No
Voltage - Maximum	277V / 480V AC
Material Info	
Engineering Number	ARC30FADE05
Reference - Drawing Numbers	
Sales Drawing	1122190052-000

EU ELV	
Not Reviewed	
EU RoHS	China RoHS
Not Reviewed	
REACH SVHC	
Not Reviewed	
Halogen-Free	
Status	
Not Reviewed	
For more information, please visit Contact US	
China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series

112219 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

1122190053