

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1122191021

Status:

Active

Overview:

Woodhead ArcArrest Connector System

Description:

Woodhead ArcArrest Plug with Handle, Drawplates, and Cap, Switch-Rated, 30.0A, 120/208V AC, 3-Pole+Neutral+Ground, Insulator Keying Position 16, Three Grommets Included



Documents:

[Drawing \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)

[Brochure \(PDF\)](#)

Agency Certification	
UL	E145922
General	
Product Family	Wiring Devices
Series	112219
IP Rating	IP69K
NEMA Configuration	N/A
Overview	Woodhead ArcArrest Connector System
Product Name	ArcArrest
Receptacle Type	N/A
Specialty	Switch-Rated
Type	Plug
UPC	78172558541
Wire Size AWG	8 to 12
Physical	
Cord Grip Body Size	F4 1"
Flange	Yes
Flip Lid	No
Gender	Male
Length	178.99mm (7.047")
Locking Blade	N/A
Poles	3
Electrical	
Cord Type	N/A
Current - Maximum per Contact	30.0A
GFCI	No
Lighted Connector	No
Voltage - Maximum	120V / 208V AC
Material Info	
Engineering Number	ARC30MHDAC05
Reference - Drawing Numbers	
Sales Drawing	1122191024-000

EU ELV	
Not Reviewed	
EU RoHS	China RoHS
Not Reviewed	
REACH SVHC	
Not Reviewed	
Halogen-Free	
Status	
Not Reviewed	
For more information, please visit Contact US	
China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series

112219 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

1122191021