

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1200845189

Status:

Active

Overview:

Description:

Ultra-Lock (M12) Receptacle, 4 Poles, M16x1.5 Mounting Threads, Female (Straight) to 0.34mm2 PVC Leads, 0.30m (11.81") Length

Agency Certification	
CSA	LR6837
General	
Product Family	Industrial Receptacles
Series	120084
IP Rating	IP69K
NEMA Rating	NEMA 6
Overview	ultralock_connection_system
Product Name	Ultra-Lock (M12)
Type	Single Ended (pigtail)
UPC	78172539533
Physical	
Coupling Type	Internal Thread
Gender	Female
Keyway	Single
Length	0.30m
Material - Component	Nickel-plated Brass
Mounting Thread Size	M16 x 1.5
Net Weight	31.356/g
Orientation	Straight
Panel Mount	Back
Poles	4
Temperature Range - Operating	-25° to +90°C
Wire Size AWG	22
Wire/Cable Type	UL 1569
Electrical	
Current - Maximum per Contact	4.0A
Voltage - Maximum	60V
Material Info	
Engineering Number	WR4W40E03C3003
Reference - Drawing Numbers	
Sales Drawing	1200845189-000

EU ELV

Not Relevant

EU RoHS

China RoHS

Compliant with Exemption 6(c)

REACH SVHC

Contained Per - D(2020)9139-DC (19 Jan 2021)

Lead

Halogen-Free Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

50 Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

120084 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

1200845189