

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1201080449

Status:

Active

Description:

Double-Ended RJ-45 Cordset, 4 Poles, Male (Straight) to Male (Straight), 24 AWG, TPE Cable, 4.0m (13.12') Length, 6.99mm (.275") Diameter, Teal

Replacement Part Number :

http://www.molex.com/molex/search/partSearch?pQuery=&sType=p&query=12010805861201080586 (drop-in)

Documents:	
Drawing (PDF)	RoHS Certificate of Compliance (PDF)

Agency Certification	
UL	E361772
General	
Product Family	Industrial Cordsets
Series	120108
Connector End A	RJ-45 (standard)
Connector End B	RJ-45 (standard)
IP Rating	IP20
Material - Contact	Copper Alloy
Performance Category	5e
Product Name	Industrial Ethernet
Protocol	EtherNet
Replacement Part Number	1201080586 (drop-in)
Type	Double Ended
UPC	78172543770
Physical	
Cable Diameter	6.99mm (.275")
Cable Length	4.0m (13.12')
Color - Cable Jacket	Teal
Coupling Style	N/A
Gender	Male-Male
Keyway	N/A
LED Indicator	No
Material - Cable Jacket	TPE
Material - Connector Body	PVC
Material - Coupling Nut	N/A
Material - Plating Mating	Gold
Orientation	Straight to Straight
Poles	4
Temperature Range - Operating	-20°C to +75°C
Wire Size AWG	24
Wire/Cable Type	TPE
Electrical	
Current - Maximum per Contact	1.5A
Voltage - Maximum	30V
Material Info	
Engineering Number	E66A06007M040
Reference - Drawing Numbers	
Sales Drawing	SD-120108-058

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Not Reviewed	
REACH SVHC	
Not Reviewed	
Halogen-Free	
Status	
Not Reviewed	
For more information, please visit Contact US	
China ROHS	Not Reviewed
ELV	Not Relevant
RoHS Phthalates	Not Reviewed

Search Parts in this Series

120108 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

1201080449