

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

**Part Number:** [1202530108](#)  
**Status:** **Active**  
**Overview:** [Contrinex Inductive and Photoelectric](#)  
**Description:** Contrinex Inductive Sensor, M18 Housing, 12mm Operating Distance, Quasi-embeddable, NPN, NO, 2m 3-wire PVC Cable, 36mm Housing Length

**Documents:**

[Product Specification 1202530108-000 \(PDF\)](#)      [RoHS Certificate of Compliance \(PDF\)](#)  
[Datasheet \(PDF\)](#)

**General**

|                  |                                                       |
|------------------|-------------------------------------------------------|
| Product Family   | Sensors                                               |
| Series           | <a href="#">120253</a>                                |
| IP Rating        | IP67                                                  |
| Overview         | <a href="#">Contrinex Inductive and Photoelectric</a> |
| Product Category | Inductive Sensors                                     |
| Product Name     | Contrinex                                             |
| Type             | Inductive                                             |
| UPC              | 191130062782                                          |

**Physical**

|                               |                        |
|-------------------------------|------------------------|
| Connection                    | Cable (PVC 2m, 3-wire) |
| Length                        | 36mm                   |
| Material - Housing            | Chrome Plated Brass    |
| Material - Sensing Face       | PBTP                   |
| Mounting Style                | Quasi-embeddable       |
| Operating Distance            | 12mm                   |
| Output                        | NO                     |
| Sensor Housing Size           | M18                    |
| Temperature Range - Operating | -25° to +70°C          |

**Electrical**

|                     |          |
|---------------------|----------|
| Polarity            | NPN      |
| Switching Frequency | ≤ 600 Hz |

**Material Info**

|                    |                   |
|--------------------|-------------------|
| Engineering Number | DW-AD-501-M18-120 |
|--------------------|-------------------|

**Reference - Drawing Numbers**

|                       |                |
|-----------------------|----------------|
| Product Specification | 1202530108-000 |
|-----------------------|----------------|



Series image - Reference only

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant with  
Exemption 6(c)**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

For more information, please visit [Contact US](#)

China ROHS

50 Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

**Search Parts in this Series**

[120253](#) Series

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[120253-0108](#)