

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1202530495

Status:

Active

Overview:

Contrinex Inductive and Photoelectric

Description:

Contrinex Inductive Sensor, 3mm Diameter Smooth Housing, 1mm Operating Distance, Embeddable, NPN, NC, 0.2m 3-wire PUR Cable, 3-pin M8 Connector, 22mm Housing Length



Documents:

Product Specification 1202530495-000 (PDF)

RoHS Certificate of Compliance (PDF)

Datasheet (PDF)

General	
Product Family	Sensors
Series	120253
IP Rating	IP67
Overview	Contrinex Inductive and Photoelectric
Product Category	Sensors
Product Name	Contrinex
Type	Inductive
UPC	191130068500
Physical	
Connection	Cable (PUR 0.2m, 3-wire), Connector (M8, 3-pin)
Length	22mm
Material - Housing	Stainless Steel
Material - Sensing Face	Polyester
Mounting Style	Embeddable
Operating Distance	1mm
Output	NC
Sensor Housing Size	3mm dia. (smooth)
Temperature Range - Operating	-25° to +70°C
Electrical	
Polarity	NPN
Switching Frequency	≤ 3000 Hz
Material Info	
Engineering Number	DW-AV-622-03-276
Reference - Drawing Numbers	
Product Specification	1202530495-000

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Reviewed	
Halogen-Free	
Status	
Not Reviewed	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

120253 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

[120253-0495](#)