

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1202540094](#)
Status: **Active**
Overview: [Contrinex Inductive and Photoelectric](#)
Description: Contrinex Photoelectric Sensor, M5 Housing, Diffuse, 10mm Operating Distance, NPN, Light-ON, 2m 3-wire PVC Cable, 35mm Housing Length

Documents:

[Product Specification 1202540094-000 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Datasheet \(PDF\)](#)

General

Product Family	Sensors
Series	120254
IP Rating	IP67
Operating Principle	Diffuse
Overview	Contrinex Inductive and Photoelectric
Product Category	Photoelectric Sensors
Product Name	Contrinex
Type	Photoelectric
UPC	191130068005

Physical

Connection	Cable (PVC 2m, 3-wire)
Length	35mm
Material - Housing	Stainless Steel
Material - Window	Sapphire
Operating Distance	10mm
Output	Light-ON
Sensor Housing Size	M5
Temperature Range - Operating	0° to +55°C

Electrical

Polarity	NPN
Switching Frequency	≤ 250 Hz

Material Info

Engineering Number	LTR-M05MA-NSK-301
--------------------	-------------------

Reference - Drawing Numbers

Product Specification	1202540094-000
-----------------------	----------------



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China RoHS

China ROHS

ELV

RoHS Phthalates

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[120254](#) Series

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

120254-0094