


13 12 11 10 9 8 7 6 5 4 3 2 1




PART NUMBER LEGEND

CC4030A70M010G

CABLE TYPE
10/4 PVC GRAY STOOW

OVERMOLD COLOR:
BLANK = GRAY
G = BLACK

FINISHED LENGTH:
M005= 0.5 METER
M010= 1 METER
M100= 10 METER



NOTES:


1. MATERIAL: SEE TABLE
2. FINISHES: SEE TABLE
3. ELECTRICAL SPECIFICATIONS
VOLTAGE RATING: 600V
CURRENT RATING: 25 AMPS
4. PROTECTION: IP67 (WHEN MATED)
5. TEMP RANGE: -20°C TO +105°C
6. COUPLING THREAD: 1 3/8-16
7. DIMS SHOWN ARE FOR REFERENCE ONLY
UNLESS OTHERWISE NOTED

10	WARNING LABEL	VINYL	BLACK/ORANGE
9	PRODUCT LABEL	VINYL	BLACK/YELLOW
8	OVERMOLDS	PVC	SEE P/N LEGEND
7	MALE COUPLING	ALUMINUM	CLEAR ANODIZED
6	CONTACT PIN	Cu ALLOY	GOLD PLATED
5	MALE INSERT, 4P	PVC	BLACK
4	FEMALE COUPLING	ALUMINUM	CLEAR ANODIZED
3	CONTACT SOCKET	Cu ALLOY	GOLD PLATED
2	FEMALE INSERT, 4C	PVC	BLACK
1	CABLE, #10/4 STOOW, HI-FLEX	PVC JACKET	GRAY/BLACK STRIPE
ITEM	DESCRIPTION	MATERIAL	FINISH

RELEASED
EC NO: IP672017-0648
DRAWN BY: RSTONE 2017/01/04
CHK'D: M. ZIELINSKI 2017/01/20
APPR'D: BWOODMAN 2017/01/18
REV: A

QUALITY SYMBOLS	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE IN/MM		SCALE 1:1	DESIGN UNITS INCH	PROJECTION
	mm	INCH	DRAWN BY	DATE			
▼=0	4 PLACES	±---	±---	RSTONE	2017/01/04	QUICK CHANGE ASSEMBLY MALE/FEMALE ST/ST 10 AWG, HI-FLEX	
▼=0	3 PLACES	±---	±---	CHECKED BY	DATE		
▼=0	2 PLACES	±---	±---	M. ZIELINSKI	2017/01/20		
▼=0	1 PLACE	±---	±---	APPROVED BY	DATE		
▼=0	0 PLACE	±---	±---	BWOODMAN	2017/01/18		
ANGULAR ±---°		MATERIAL NO.		DOCUMENT NO.	SHEET NO.		
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		-		SD-130064-021	1 OF 1		
C		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION					

13 12 11 10 9 8 7 6 5 4 3 2 1




PART NUMBER LEGEND

CC4030A70M010G

CABLE TYPE
10/4 PVC GRAY STOOW

OVERMOLD COLOR:
BLANK = GRAY
G = BLACK

FINISHED LENGTH:
M005= 0.5 METER
M010= 1 METER
M100= 10 METER



NOTES:

1. MATERIAL: SEE TABLE
2. FINISHES: SEE TABLE
3. ELECTRICAL SPECIFICATIONS
VOLTAGE RATING: 600V
CURRENT RATING: 25 AMPS
4. PROTECTION: IP67 (WHEN MATED)
5. TEMP RANGE: -20°C TO +105°C
6. COUPLING THREAD: 1 3/8-16
7. DIMS SHOWN ARE FOR REFERENCE ONLY
UNLESS OTHERWISE NOTED

10	WARNING LABEL	VINYL	BLACK/ORANGE
9	PRODUCT LABEL	VINYL	BLACK/YELLOW
8	OVERMOLDS	PVC	SEE P/N LEGEND
7	MALE COUPLING	ALUMINUM	CLEAR ANODIZED
6	CONTACT PIN	Cu ALLOY	GOLD PLATED
5	MALE INSERT, 4P	PVC	BLACK
4	FEMALE COUPLING	ALUMINUM	CLEAR ANODIZED
3	CONTACT SOCKET	Cu ALLOY	GOLD PLATED
2	FEMALE INSERT, 4C	PVC	BLACK
1	CABLE, #10/4 STOOW, HI-FLEX	PVC JACKET	GRAY/BLACK STRIPE
ITEM	DESCRIPTION	MATERIAL	FINISH

RELEASED
EC NO: IP672017-0648
DRAWN BY: RSTONE 2017/01/04
CHK'D: M. ZIELINSKI 2017/01/20
APPR'D: BWOODMAN 2017/01/18
REV: A

QUALITY SYMBOLS	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE IN/MM		SCALE 1:1	DESIGN UNITS INCH	PROJECTION
	mm	INCH	DRAWN BY	DATE			
▼=0	4 PLACES	±---	±---	RSTONE	2017/01/04	QUICK CHANGE ASSEMBLY MALE/FEMALE ST/ST 10 AWG, HI-FLEX	
▼=0	3 PLACES	±---	±---	CHECKED BY	DATE		
▼=0	2 PLACES	±---	±---	M. ZIELINSKI	2017/01/20		
▼=0	1 PLACE	±---	±---	APPROVED BY	DATE		
▼=0	0 PLACE	±---	±---	BWOODMAN	2017/01/18		
ANGULAR ±---°		MATERIAL NO.		DOCUMENT NO.	SHEET NO.		
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		-		SD-130064-021	1 OF 1		
C		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION					

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex](#):

[1300640411](#)