

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1300980204](#)
Status: **Active**
Overview: [Strain-Relief Cord Grips](#)
Description: MAX-LOC Multi-Hole Strain Relief, 1/2" NPT, Straight Male, Cable Diameter 4.75mm (.187")

Documents:
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Brochure \(PDF\)](#)

Agency Certification	
CSA	LR32159
General	
Product Family	Cable Grips
Series	130098
Comments	Indicates that one or more grommet hole is covered by a thin membrane which can easily be "Poked" open if required.
Eye Type	N/A
NEMA Rating	NEMA 3R
O-Ring	No
Overview	Strain-Relief Cord Grips
Product Name	MAX-LOC
Type	Strain Relief Grip
UPC	78678850421
Use With	1/2" NPT MAX-LOC Lock Nut 1300990143 , MAX-LOC O-Ring, 1/2" NPT 1301800314 , 1/2" NPT MAX-LOC Gasket 1300990149
Physical	
Approximate Break Strength	N/A
Bale Length	N/A
Body Style	Straight
Cable Diameter	4.75mm (.187")
Color - Grommet	Yellow
Gender	Male
Material - Body	Nylon
Material - Grip	N/A
Mesh Length	N/A
Number of Holes	2, 3, 4, 5, 6, or 7
Thread Size	1/2" NPT
Material Info	
Engineering Number	5594-008
Reference - Drawing Numbers	
Sales Drawing	SD-130098-195



Series image - Reference only

EU ELV Not Reviewed	
EU RoHS Not Reviewed REACH SVHC Not Reviewed Halogen-Free Status Not Reviewed	China RoHS
For more information, please visit Contact US	
China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series
[130098](#) Series

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[1300980204](#)