

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1301530263

Status:

Active

Overview:

Ground Fault Circuit Interrupter (GFCI) Products

Description:

Super-Safeway Fixed Mount GFCI, Automatic Reset, Flying Leads, 30A, 120V, 0.61m (2.0') Wire Length

Documents:	
Drawing (PDF)	RoHS Certificate of Compliance (PDF)

General	
Product Family	Power Distribution
Series	130135
Enclosure Rating	N/A
GFCI Reset	Automatic
Mounting Style	Permanent
Open Neutral Relay	Yes
Overview	Ground Fault Circuit Interrupter (GFCI) Products
Product Name	Super-Safeway
Receptacle Type	N/A
Type	GFCI Industrial Duty, Single Phase
UPC	78172544359
Physical	
Cord Diameter	N/A
Cord Grip Body Size	N/A
Cord Length	0.61m (2.0')
Feed-Thru	No
Flip Lid	No
Material - Housing	Nylon
Number of Receptacles	0
Packaging Type	Carton
Electrical	
Cord Type	10/3 THHN
Current - Maximum per Contact	30.0A
GFCI	Yes
Ground Continuity Monitor	No
NEMA Configuration	N/A
Voltage - Maximum	120V
Material Info	
Engineering Number	30051-2AF

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Not Reviewed	
REACH SVHC	
Not Reviewed	
Halogen-Free	
Status	
Not Reviewed	
For more information, please visit Contact US	
China ROHS	Not Reviewed
ELV	Not Relevant
RoHS Phthalates	Not Reviewed

Search Parts in this Series

130135 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

1301530263