

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1600280005

Status:

Active

Overview:

stak50h\_unsealed\_connection\_system...

Description:

AK50 HYBRID RCPT 32 CKT PINK KEY 5

Documents:

3D Model

3D Model (PDF)

Drawing (PDF)

Datasheet (PDF)

RoHS Certificate of Compliance (PDF)

Application tooling part link

Application Tooling Part Link

200222-0100

General

Product Family

Series

Application

Overview

Product Name

UPC

Crimp Housings

160028

Automotive, Power, Signal, Wire-to-Board

stak50h\_unsealed\_connection\_system...

stAK50h

889056387552

Physical

Circuits (maximum)

Color - Resin

Gender

Glow-Wire Capable

Keying to Mating Part

Lock to Mating Part

Material - Resin

Net Weight

Number of Rows

Packaging Type

Panel Mount

Pitch - Mating Interface

Pitch - Termination Interface

Polarized to Mating Part

Ports

Stackable

Temperature Range - Operating

32

Pink

Receptacle

No

Yes

Yes

SPS

5.360/g

5

Bag

No

2.00mm, 4.00mm

2.00mm, 4.00mm

Yes

1

No

-40° to +85°C

Material Info



Series image - Reference only

EU ELV

Compliant

EU RoHS

Compliant

REACH SVHC

Not Contained Per - ECHA\_01\_2020 (16 January 2020)

Halogen-Free

Status

Not Relevant

For more information, please visit [Contact US](#)

China RoHS

Not Relevant

ELV

Compliant

RoHS Phthalates

Not Contained

Search Parts in this Series

160028 Series

Use With

TE NanoMQS 0.50mm Terminal|Delphi OCS 1.20mm T...

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description

Product #

Extraction Tool for stAK50h Connector System

2002220100

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

160028-0005