

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1731070124](#)
Status: **Active**
Overview: [FCT D-Sub Connectors](#)
Description: FCT Mixed Layout D-Sub Housing, Female, Tin-plated Shell without Dimples, 7 Circuits

Documents:
[Datasheet \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Brochure \(PDF\)](#)

General
Product Family D-Sub Products
Series [173107](#)
IP Rating IP20
Overview [FCT D-Sub Connectors](#)
Product Category D-Sub Connector
Product Name FCT Products
Type Mixed Layout
UPC 889056485005

Physical
Circuits (Loaded) 0
Circuits (maximum) 7
Color - Resin Black
Gender Female
Material - Resin PBT
Material - Shell Steel
Net Weight 10.300/g
Number of Rows 1
PCB Locator No
PCB Retention None
Packaging Type Carton
Panel Mount Rear
Panel Mount Method Flange
Plating - Shell Tin
Polarized to Mating Part Yes
Ports 1
Shielded Yes
Temperature Range - Operating -55° to +130°C
Waterproof / Dustproof No
Waterproof / Dustproof Type IP20

Material Info
Engineering Number F7W7S-K121



Series image - Reference only

EU ELV
Not Relevant

EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - D(2020)4578-DC (25 June 2020)	
Halogen-Free	
Status	
Not Reviewed	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series
[173107 Series](#)

Mates With
FCT Mixed Layout D-Sub, Size 4, 7W7, Plug

Use With
FCT Coaxial, High Power, High Voltage, or Pneumatic Contacts

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[173107-0124](#)