

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1731070175](#)
Status: **Active**
Overview: [FCT D-Sub Connectors](#)
Description: FCT Mixed Layout D-Sub Crimp Housing, Male, Tin-plated Shell with Dimples, 21 Circuits, 17 Unloaded Signal Contact Positions

Documents:

[Datasheet \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Brochure \(PDF\)](#)

General

Product Family	D-Sub Products
Series	173107
IP Rating	IP20
Overview	FCT D-Sub Connectors
Product Category	D-Sub Connector
Product Name	FCT Products
Type	Mixed Layout
UPC	889056485517

Physical

Circuits (Loaded)	0
Circuits (maximum)	21
Color - Resin	Black
Durability (mating cycles max)	500
Gender	Male
Material - Resin	PBT
Material - Shell	Steel
Net Weight	10.200/g
Number of Rows	2
Orientation	Straight
PCB Locator	No
PCB Retention	None
Packaging Type	Carton
Panel Mount	Rear
Panel Mount Method	Flange
Pitch - Mating Interface	2.84mm
Pitch - Termination Interface	2.84mm
Plating - Shell	Tin
Polarized to Mating Part	Yes
Ports	1
Shielded	Yes
Temperature Range - Operating	-55° to +115°C
Waterproof / Dustproof	No
Waterproof / Dustproof Type	IP20
Wire Size AWG	18, 20, 22, 24, 26, 28

Material Info

Engineering Number FL21WA4P7-K120



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

**Compliant with
Exemption 6(c)**

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China RoHS

China ROHS	50 Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

[173107 Series](#)

Mates With

FCT Mixed Layout D-Sub, Size 4, 21WA4, Socket

Use With

FCT Coaxial, High Power, High Voltage, or Pneumatic Contacts

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[173107-0175](#)