

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [2053410202](#)
Status: **Active**
Overview: [Pico-Lock Connector System](#)
Description: 2.00mm Pitch, Pico-Lock Receptacle Crimp Housing, Single Row, Positive Lock, 2 Circuits, Black

Documents:
[3D Model](#) [Application Specification 2053410000-AS-000 \(PDF\)](#)
[Drawing \(PDF\)](#) [Packaging Specification 2053419200-SPK-200 \(PDF\)](#)
[3D Model \(PDF\)](#) [Datasheet \(PDF\)](#)
[Product Specification 2053410000-PS-000 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General	
Product Family	Crimp Housings
Series	205341
Application	Signal, Wire-to-Board
Overview	Pico-Lock Connector System
Product Name	Pico-Lock
UPC	191130509973
Physical	
Circuits (maximum)	2
Color - Resin	Black
Gender	Receptacle
Glow-Wire Capable	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Resin	Polyamide
Net Weight	98.950/mg
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	2.00mm
Polarized to Mating Part	Yes
Temperature Range - Operating	-40° to +105°C

Material Info

Reference - Drawing Numbers

Application Specification	2053410000-AS-000
Packaging Specification	2053419200-SPK-200
Product Specification	2053410000-PS-000
Sales Drawing	2053410000-SD-000



Series image - Reference only

EU ELV Not Relevant	
EU RoHS Compliant REACH SVHC Not Contained Per - D(2021)4569-DC (8 July 2021) Halogen-Free Status Low-Halogen For more information, please visit Contact US	China RoHS China ROHS ELV RoHS Phthalates
	Green Image Not Relevant Not Contained

Search Parts in this Series
[205341](#) Series

Mates With
Pico-Lock PCB Header [205338](#)

Use With
Pico-Lock Crimp Terminal [205342](#)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[205341-0202](#)