

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [2125141006](#)
Status: **Active**
Overview: Mini-Fit Family Power Connectors
Description: Mini-Fit Max Receptacle Housing, Dual Row, UL 94V-0, 6 Circuits, Glow-Wire Capable, Black

Documents:

- [Drawing \(PDF\)](#)
[Product Specification 2125150000-PS-000 \(PDF\)](#)
[Packaging Specification 2125140001-PK-000 \(PDF\)](#)
- [Datasheet \(PDF\)](#)
[RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Crimp Housings
Series	212514
Application	Power, Wire-to-Board, Wire-to-Wire
Overview	Mini-Fit Family Power Connectors
Product Name	Mini-Fit Max
UPC	193264598267

Physical

Circuits (maximum)	6
Color - Resin	Black
Gender	Receptacle
Glow-Wire Capable	Yes
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Resin	Nylon
Net Weight	1.550/g
Number of Rows	2
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	4.20mm
Pitch - Termination Interface	4.20mm
Polarized to Mating Part	Yes
Temperature Range - Operating	-40° to +105°C

Material Info

Reference - Drawing Numbers

Packaging Specification	2125140001-PK-000
Product Specification	2125150000-PS-000
Sales Drawing	2125140001-SD-000



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2021)4569-DC (8
July 2021)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China RoHS

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

[212514](#) Series

Mates With

Mini-Fit Max Header [212520](#)

Use With

Mini-Fit Max Crimp Terminal [212515](#) . Mini-Fit Max TPA [2125161003](#)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[212514-1006](#)