

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: **5023810000**
Status: **Active**
Overview: CLIK-Mate Wire-to-Board Connectors
Description: CLIK-Mate and IllumiMate 1.25mm Pitch Wire-to-Board Crimp Terminal, Tin Plating, Reel

Documents:

3D Model (PDF)	Product Specification PS-502382-001-001 (PDF)
Drawing (PDF)	Packaging Specification SPK-502381-001-001 (PDF)
3D Model	RoHS Certificate of Compliance (PDF)
Product Specification 2028120000-000 (PDF)	



General

Product Family	Crimp Terminals
Series	502381
Application	Signal, Wire-to-Board
Crimp Quality Equipment	Yes
Overview	CLIK-Mate Wire-to-Board Connectors
Product Name	CLIK-Mate, IllumiMate
UPC	822350895187

Physical

Durability (mating cycles max)	30
Gender	Male
Material - Metal	Copper Alloy
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	29.658/mg
Packaging Type	Reel
Plating min - Mating	0.406µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	0.80-1.0mm
Wire Size AWG	26, 28
Wire Size mm ²	0.08-0.13

Electrical

Current - Maximum per Contact	1.0A
Voltage - Maximum	50V AC (RMS)/DC

Material Info

Reference - Drawing Numbers

Crimp Specification	CS-502381-001-001
Packaging Specification	SPK-502381-001-001
Product Specification	2028120000-000, PS-502382-001-001
Sales Drawing	SD-502381-001

EU ELV

Compliant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2020)4578-DC (25
June 2020)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Compliant

Not Contained

Search Parts in this Series

[502381](#) Series

Use With

CLIK-Mate Housing [502380](#)

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
Extraction and Activation Tool	638132700
Hand Tool for 1.25mm Wire-to-Board Crimp Terminal, 26-28 AWG Wire	638194400
FineAdjust Applicator for 1.25mm Pitch Wire-to-Board Connector Dual Plug	639006600

Terminals, 26-28
AWG

T2 Terminator 639106600

Tooling Die for
1.25mm Pitch Wire-
to-Board Connector
Dual Plug Terminals,
26-28 AWG

Japan

Description **Product #**

Applicator for M211A 5780343000

Bench Press, 26-28

AWG Wire

S-1 Applicator for 5780343700

Duo-Clasp, CLIK-

Mate, IllumiMate

Terminals, 26-28

AWG

This document was generated on 09/14/2020

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[502381-0000](#) [502381-0000 \(Cut Strip\)](#) [502381-0000 \(Mouser Reel\)](#) [502381-0000 \(Loose Piece\)](#)