

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

5023861470

Status:

Active

Overview:

CLIK-Mate Wire-to-Board Connectors

Description:

1.25mm Pitch CLIK-Mate Wire-to-Board PCB Receptacle, Single Row, Right-Angle, Tin (Sn) Plating, 14 Circuits

Documents:

- Drawing (PDF)

Application Specification AS-502380-002-001 (PDF)
- 3D Model (PDF)

Packaging Specification SPK-502386-001-001 (PDF)
- 3D Model

RoHS Certificate of Compliance (PDF)
- Product Specification PS-502382-001-001 (PDF)

Agency Certification

UL

E29179

General

Product Family

Series

Application

Overview

Product Name

UPC

PCB Receptacles

502386

Signal, Wire-to-Board

CLIK-Mate Wire-to-Board Connectors

CLIK-Mate

822350895798

Physical

Circuits (Loaded)

Circuits (maximum)

Color - Resin

Durability (mating cycles max)

Glow-Wire Capable

Guide to Mating Part

Keying to Mating Part

Lock to Mating Part

Mated Height

Material - Metal

Material - Plating Mating

Material - Plating Termination

Material - Resin

Net Weight

Number of Rows

Orientation

PCB Locator

PCB Retention

Packaging Type

Pitch - Mating Interface

Pitch - Termination Interface

Plating min - Mating

Plating min - Termination

Polarized to Mating Part

Polarized to PCB

Stackable

Surface Mount Compatible (SMC)

Temperature Range - Operating

Termination Interface: Style

14

14

Natural

30

No

Yes

Yes

Yes

5.55mm

Copper Alloy

Tin

Tin

High Temperature Thermoplastic

599.201/mg

1

Right Angle

No

Yes

Embossed Tape on Reel

1.25mm

1.25mm

1.016µm

1.016µm

Yes

No

No

Yes

-40° to +105°C

Surface Mount

Electrical

Current - Maximum per Contact

Voltage - Maximum

1.0A

50V AC (RMS)/DC



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2021)4569-DC (8
July 2021)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

502386 Series

Mates With

502380 CLIK-Mate Housing

Material Info

Reference - Drawing Numbers

Application Specification	AS-502380-002-001
Packaging Specification	SPK-502386-001-001
Product Specification	PS-502382-001-001
Sales Drawing	SD-502386-002-001, SD-502386-002-002, SD-502386-002-003, SD-502386-003-001, SD-502386-003-002

This document was generated on 10/05/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[502386-1470](#)