

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

5055680681

Status:

Active

Overview:

Micro-Lock Plus Wire-to-Board Connector System

Description:

1.25mm Pitch, Micro-Lock Plus PCB Header, Single Row, Vertical, Surface Mount, 0.10µm Gold Plating, Positive Lock, 6 Circuits, with Pick-and-Place Polyimide Tape, Black

- Documents:
- 3D Model

Application Specification AS-505565-001-001 (PDF)
- 3D Model (PDF)

Packaging Specification 5055689200-200 (PDF)
- Drawing (PDF)

Datasheet (PDF)
- Product Specification 5055650002-000 (PDF)

RoHS Certificate of Compliance (PDF)
- Product Specification 5055651002-PS-000 (PDF)

Agency Certification	
UL	E29179
General	
Product Family	PCB Headers
Series	505568
Application	Signal, Wire-to-Board
Overview	Micro-Lock Plus Wire-to-Board Connector System
Product Name	Micro-Lock Plus
UPC	889056857536
Physical	
Breakaway	No
Circuits (Loaded)	6
Circuits (maximum)	6
Color - Resin	Black
Durability (mating cycles max)	30
First Mate / Last Break	No
Glow-Wire Capable	No
Guide to Mating Part	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Metal	Brass
Material - Plating Mating	Gold
Material - Plating Termination	Gold
Material - Resin	Polyamide
Net Weight	204.000/mg
Number of Rows	1
Orientation	Vertical
PCB Locator	No
PCB Retention	Yes
Packaging Type	Embossed Tape on Reel
Pitch - Mating Interface	1.25mm
Pitch - Termination Interface	1.25mm
Plating min - Mating	0.100µm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Robotic Placement	Vacuum Pick-Up Tape
Stackable	No
Temperature Range - Operating	-40° to +105°C
Termination Interface: Style	Surface Mount

Electrical



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

China RoHS

Compliant

REACH SVHC

Not Contained Per -

D(2021)4569-DC (8

July 2021)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit

Contact US

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

505568 Series

Mates With

Micro-Lock Plus Receptacle Housing

505565

Current - Maximum per Contact

1.5A

Voltage - Maximum

50V AC (RMS)/DC

Material Info

Reference - Drawing Numbers

Application Specification

AS-505565-001-001

Packaging Specification

5055689200-200

Product Specification

5055650002-000, 5055651002-PS-000

Sales Drawing

5055680010-SD-000

This document was generated on 10/04/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

505568-0681