

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

2065230161

Status:

Active

Overview:

Mini50 Connection Systems

Description:

Mini50 Unsealed Receptacle, Dual Row, UL94-HB, without CPA, 16 Circuits, Polarization Option A, Black



Series image - Reference only

Documents:	
3D Model	Product Specification 2065230000-PS-000 (PDF)
3D Model (PDF)	Packaging Specification PK-31301-538-001 (PDF)
Drawing (PDF)	RoHS Certificate of Compliance (PDF)

General	
Product Family	Crimp Housings
Series	206523
Application	Automotive, Power, Wire-to-Board
Overview	Mini50 Connection Systems
Polarization	A
Product Name	Mini50
UPC	191130110018
Physical	
Circuits (maximum)	16
Color - Resin	Black
Gender	Receptacle
Glow-Wire Capable	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Resin	PBT
Net Weight	1.687/g
Number of Rows	2
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	2.00mm
Pitch - Termination Interface	2.00mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40° to +100°C

Material Info	
Reference - Drawing Numbers	
Packaging Specification	PK-31301-538-001
Product Specification	2065230000-PS-000
Sales Drawing	2065230000-000

EU ELV
Compliant

EU RoHS Compliant REACH SVHC Not Contained Per - D(2021)4569-DC (8 July 2021) Halogen-Free Status Low-Halogen	China RoHS
---	-------------------

For more information, please visit [Contact US](#)

China ROHS	Green Image
ELV	Compliant
RoHS Phthalates	Not Contained

Search Parts in this Series
206523 Series

Mates With
Mini50 Surface Mount Header [348978160](#)
, [348979160](#)
 Mini50 Vertical Through-Hole Header [348250160](#) , [348259160](#)
 Mini50 Right-Angle Through-Hole Header [348260160](#) , [348269160](#)

Use With
CTX50 Unsealed Terminals [560023](#)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[206523-0161](#)