

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

2065230163

Status:

Active

Overview:

Mini50 Connection Systems

Description:

Mini50 Unsealed Receptacle, Dual Row, UL94-HB, without CPA, 16 Circuits, Polarization Option A, Black



Series image - Reference only

Documents:	
3D Model	Product Specification 2065230000-PS-000 (PDF)
Drawing (PDF)	Packaging Specification PK-31301-538-001 (PDF)
3D Model (PDF)	RoHS Certificate of Compliance (PDF)

General	
Product Family	Crimp Housings
Series	206523
Application	Automotive, Power, Wire-to-Board
Overview	Mini50 Connection Systems
Polarization	C
Product Name	Mini50
UPC	191130110032
Physical	
Circuits (maximum)	16
Color - Resin	Gray (Dark)
Gender	Receptacle
Glow-Wire Capable	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Resin	PBT
Net Weight	1.687/g
Number of Rows	2
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	2.00mm
Pitch - Termination Interface	2.00mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40° to +100°C

Material Info	
Reference - Drawing Numbers	
Packaging Specification	PK-31301-538-001
Product Specification	2065230000-PS-000
Sales Drawing	2065230000-000

EU ELV Compliant	
EU RoHS Compliant	China RoHS
REACH SVHC Not Contained Per - D(2021)4569-DC (8 July 2021)	
Halogen-Free Status Low-Halogen	
For more information, please visit Contact US	
China ROHS ELV	Green Image Compliant
RoHS Phthalates	Not Contained

Search Parts in this Series
206523 Series

Mates With
Mini50 Surface Mount Header [348978162](#)
, [348979162](#)
 Mini50 Vertical Through-Hole Header [348250162](#) , [348259162](#)
 Mini50 Right-Angle Through-Hole Header [348260162](#) , [348269162](#)

Use With
CTX50 Unsealed Terminals [560023](#)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[206523-0163](#)