

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

2073711001

Status:

Active

Overview:

[SlimSAS Connectors and Cable Assemblies](#)

Description:

SlimSAS Cable Assembly, PCIe 4.0, Straight Plug-to-Straight Plug, 4x (38 Circuits), 32 AWG, 0.30m Length



Documents:

[Drawing \(PDF\)](#)

[Application Specification 2073680002-000 \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)

General	
Product Family	Cable Assemblies
Series	207371
Assembly Configuration	Dual Ended Connectors
Connector to Connector	SlimSAS-to-SlimSAS
Overview	SlimSAS Connectors and Cable Assemblies
Product Name	SlimSAS
UPC	191130022755
Physical	
Cable Length	0.30m
Circuits (Loaded)	38
Color - Resin	Black
Gender	Plug/Plug
Lock to Mating Part	Yes
Material - Resin	Polycarbonate
Net Weight	16.000/g
Packaging Type	Bag
Single Ended	No
Wire Size AWG	32
Wire/Cable Type	Ribbon Cable
Electrical	
Current - Maximum per Contact	0.5A
Impedance	85Ω
Voltage - Maximum	30V AC
Material Info	
Reference - Drawing Numbers	
Application Specification	2073680002-000
Sales Drawing	2073681000-000

EU ELV	
Not Reviewed	
EU RoHS	China RoHS
Not Reviewed	
REACH SVHC	
Not Reviewed	
Halogen-Free	
Status	
Not Reviewed	
For more information, please visit Contact US	
China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series

[207371](#) Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[207371-1001](#)