

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0002065100

Status:

Active

Overview:

Standard .062"+ and Standard .062" Pin and Socket Connector Systems

Description:

1.57mm Diameter, Standard .062" Pin and Socket Crimp Terminal, Female, with 0.38µm Gold (Au) Plated Brass Contact, 18-24 AWG, Reel

Documents:

Drawing (PDF)

Packaging Specification 15610000-PK-000 (PDF)

RoHS Certificate of Compliance (PDF)

General	
Product Family	Crimp Terminals
Series	1561
Application	Power, Wire-to-Wire
Crimp Quality Equipment	Yes
Overview	Standard .062"+ and Standard .062" Pin and Socket Connector Systems
Packaging Alternative	02065103 (Loose)
Product Name	Standard .062"
UPC	800753615731
Physical	
Gender	Female
Material - Metal	Brass
Material - Plating Mating	Gold
Material - Plating Termination	Nickel
Net Weight	0.080/g
Packaging Type	Reel
Plating min - Mating	0.381µm
Plating min - Termination	0.762µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.52-3.05mm
Wire Size AWG	18, 20, 22, 24
Wire Size mm²	N/A
Solder Process Data	
Lead-freeProcess Capability	N/A
Material Info	
Engineering Number	1561-(P550)
Reference - Drawing Numbers	
Packaging Specification	15610000-PK-000
Sales Drawing	SD-1561-X-001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per -

D(2021)4569-DC (8

July 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit

Contact US

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

1561 Series

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global	
Description	Product #
Insertion Tool for Standard .062" Diameter Male and Female Terminals	11020001
Extraction Tool for Standard .062" and Standard .062"+ Pin and Socket Terminals	11030002
Terminator Die	11402004
ServiceGrade Hand Crimp Tool for Field Repair Only, 14-24 AWG	638111000

Hand Crimp Tool for [638191300](#)
Standard 1.57mm
Pin and Socket
Crimp Terminals,
18-24 AWG
Mini-Mac Applicator [638914000](#)
for Standard .062"
Pin and Socket
Terminals, for 18-24
AWG Wire with
Insulation Diameter
1.52-3.05mm

This document was generated on 02/08/2022

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[02-06-5100](#)