

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: 0008500023
Status: Active
Overview: KK Interconnect Solutions
Description: KK 396 Crimp Terminal 8818, 18-22 AWG, Bag, Brass Tin (Sn)

Documents:
[Drawing \(PDF\)](#)
[Product Specification PS-08-50-001 \(PDF\)](#)
[Packaging Specification PK-2759-001-001 \(PDF\)](#)
[RoHS Certificate of Compliance \(PDF\)](#)

General
Product Family Crimp Terminals
Series 8818
Application Power, Wire-to-Board
Crimp Quality Equipment Yes
Overview KK Interconnect Solutions
Packaging Alternative 08500008 (Reel)
Product Name KK 396
UPC 800754233217

Physical
Gender Female
Material - Metal Brass
Material - Plating Mating Tin
Material - Plating Termination Tin
Net Weight 0.180/g
Packaging Type Bag
Plating min - Mating 2.540µm
Plating min - Termination 2.540µm
Termination Interface: Style Crimp or Compression
Wire Insulation Diameter 2.41mm max.
Wire Size AWG 18, 20, 22
Wire Size mm² N/A

Solder Process Data
Lead-freeProcess Capability N/A

Material Info
Engineering Number 8818-(P909)L

Reference - Drawing Numbers
Packaging Specification PK-2759-001-001
Product Specification PS-08-50-001
Sales Drawing SD-8818-001



Series image - Reference only

EU ELV
Not Relevant

EU RoHS **China RoHS**
Compliant
REACH SVHC
Not Contained Per -
D(2021)4569-DC (8
July 2021)
Halogen-Free
Status
Low-Halogen
For more information, please visit [Contact US](#)

China ROHS Green Image
ELV Not Relevant
RoHS Phthalates Not Contained

Search Parts in this Series
8818 Series

Application Tooling | FAQ
Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.
Global

Description	Product #
Hand Crimp Tool for 3.96mm Pitch KK Crimp Terminals, 18-22 AWG	638280300

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[08-50-0023](#)