

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0010011124

Status:

Active

Overview:

KK 508 Connector System

Description:

5.08mm Pitch KK Crimp Terminal Housing, 12 Circuits, Natural

Documents:	
3D Model	Product Specification PS-99020-0087-001 (PDF)
Drawing (PDF)	Packaging Specification 30010001-PK-000 (PDF)
3D Model (PDF)	RoHS Certificate of Compliance (PDF)

Agency Certification

CSA	LR19980
UL	E29179

General

Product Family	Crimp Housings
Series	3001
Application	Power, Wire-to-Board
Overview	KK 508 Connector System
Product Name	KK 508
UPC	800753612754

Physical

Circuits (maximum)	12
Color - Resin	Natural
Flammability	94V-2
Gender	Receptacle
Glow-Wire Capable	No
Material - Resin	Nylon
Net Weight	3.251/g
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	5.08mm
Temperature Range - Operating	See Product Specification

Solder Process Data

Lead-freeProcess Capability	WAVE
-----------------------------	------

Material Info

Engineering Number	3001-12
--------------------	---------

Reference - Drawing Numbers

Packaging Specification	30010001-PK-000
Product Specification	PS-99020-0087-001
Sales Drawing	SDE-3001-N-X-001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per -
D(2021)4569-DC (8
July 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

3001 Series

Mates With

Headers [3061](#) , [3003](#) , [3061](#)

Use With

Crimp Terminals [2478](#) , [2578](#) , [2878](#)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

10-01-1124