

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0011184115](#)
Status: **Active**
Overview: [Application Tooling](#)
Description: [Conductor Anvil](#)


Documents:
[RoHS Certificate of Compliance \(PDF\)](#)

General
Product Family [Application Tooling](#)
Series [207126](#)
Comments [See Tooling Specification \(PDF\) Above](#)
Function [Cutter](#)
Geographic Area [Global](#)
Level of Automation [Semi-Automatic](#)
More Detailed Tech Information [applicationtooling@molex.com](#)
Overview [Application Tooling](#)
Product Name [N/A](#)
Tool Type [Applicator](#)
UPC [800753181342](#)
Warranty Disclaimer [CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors \("Molex Tooling"\). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.](#)

Physical
Net Weight [4.040/g](#)

Material Info
Engineering Number [60712 15](#)

Reference - Drawing Numbers
[Application Tooling Documents](#) [ATS-STANDARD-PARTS-001](#)



EU ELV
Not Relevant

EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - D(2020)9139-DC (19 Jan 2021)	
Halogen-Free Status	
Not Relevant	
For more information, please visit Contact US	
China ROHS	Not Relevant
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series
[207126 Series](#)

Use With
[11182022](#) , [11183021](#) , [638881000](#) , [638881070](#)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[11-18-4115](#)